

OTICON | Opn

Product comparison

	Oticon Opn 1	Oticon Opn 2	Oticon Opn 3
Speech Understanding			
OpenSound Navigator™	Level 1	Level 2	Level 3
- Balancing power effect	100%	50%	50%
- Max. noise removal	9 dB	5 dB	3 dB
Speech Guard™ LX	Level 1	Level 2	Level 3
Spatial Sound™ LX	4 estimators	2 estimators	2 estimators
Soft Speech Booster LX	•	•	•
Sound Quality			
Clear Dynamics	•	•	-
Spatial Noise Management	•	•	-
Fitting Bandwidth	10 kHz	8 kHz	8 kHz
Processing Channels	64	48	48
Bass Boost (streaming)	•	•	•
Listening Comfort			
Transient Noise Management	4 configurations	On/Off	On/Off
Feedback shield LX	•	•	•
Wind Noise Management	•	•	•
Binaural Coordination	•	•	•
Personalisation & Optimising Fitting			
YouMatic™ LX	3 configurations	2 configurations	1 configuration
Fitting Bands	16	14	12
Multiple Directionality Options	•	•	•
Adaptation Management	•	•	•
Oticon Firmware Updater	•	•	•
Fitting Formulas	VAC+, NAL-NL1 + 2	VAC+, NAL-NL1 + 2	VAC+, NAL-NL1 + 2
Acoustic Notifications	•	•	•
Connecting to the World			
Stereo streaming (2.4 GHz)	•	•	•
Made for iPhone®	•	•	•
Oticon ON App	•	•	•
ConnectClip	•	•	•
Remote Control 3.0	•	•	•
TV Adapter 3.0	•	•	•
Autophone	•	•	•



TwinLink
NFMI + 2.4 GHz

oticon
PEOPLE FIRST